




SERVICE JIG 5003-MT-1



SERVICE TOOLS

PNEUMATIC TORQUE WRENCH 5003-MT-2 **SPECIAL ORDER ONLY**

**6 & 8 MM
HEXAGON BITS**
for 1/2" drive


5003-MT-3-6
6 MM HEX BIT
for 8 MM Cap Screw

5003-MT-3-8
8 MM HEX BIT
for 10 MM Cap Screw

**POWER SUPPLY: COMPRESSED
AIR: 7 l/s, 600 kPa**

LUBRICATION


COMBINED NOZZLE 5003-MT-4-5




MODEL 5003-MT-1-KIT SERVICE/REPAIR TOOL KIT contains:

QTY.	MODEL	DESCRIPTION
1	5003-076174735987	DEWALT 15-GALLON JOB BOX CHEST w/ WHEELS
1	5003-MT-1	SERVICE JIG for C5AM, C5AM-DF, C8A-DF & CV-20
1	5003-MT-1-TS	TOGGLE SPINDLE attached to MT-1 SERVICE JIG (used on C5AM & C5AM-DF locks)
1	5003-MT-1-SP	SPRING TENSIONER for MT-1 SERVICE JIG (used on C5AM & C5AM-DF locks)
1	5003-107423	RATCHET WRENCH w/ 1/ 2" DRIVE
1	5003-684254	5" RATCHET EXTENSION w/ 1/ 2" DRIVE
4	5003-MT-3-6	6 MM HEX BIT for M8 Cap Screw
1	5003-MT-3-8	8 MM HEX BIT for M10 Cap Screw

GREASE PUMP PORTABLE GREASE DISPENSER 5003-MT-6 **SPECIAL ORDER ONLY**



RATCHET WRENCH w/ 1/ 2" drive **5003-107423**



5" RATCHET EXTENSION w/ 1/ 2" drive **5003-684254**



GREASE


5003-MT-7






5003-ET-1
WOODEN EMERGENCY TOOL

FRONT OPERATING




5003-ET-2
STEEL EMERGENCY TOOL


SIDE OPERATING




MODEL	MATERIAL	WEIGHT	COLOR	REMARK
5003-ET-1	HICKORY WOOD	0.15 Kg / 0.34 LBS	RED	FRONT OPERATING
5003-ET-2	STEEL	0.66 Kg / 1.45 LBS	RED	SIDE OPERATING



USE THE EMERGENCY TOOL:




WHEN THE
WIRE-HANDLE
IS OUT OF
FUNCTION.




WHEN THE
TWISTLOCK
HAS BEEN
MOUNTED
BACKWARDS/
FRONT.




**USED WHEN UNLOCKING HANDLE IS TORN OFF OR
POINTING THE WRONG WAY UNDER THE CONTAINER.**



1
**WHEN THE TWISTLOCK IS ACCESSIBLE
FROM FRONT, USE TOOL: 5003-ET-1.**




2
**TWIST THE UPPER CONE
COUNTER-CLOCKWISE BY PUSHING
THE TOOL INTO THE CORNER CASTING.**




3
**MAKE SURE THAT THE TOOL IS SECURED
BEFORE LIFTING THE CONTAINER.**




**USED WHEN UNLOCKING HANDLE IS TORN OFF OR
POINTING THE WRONG WAY UNDER THE CONTAINER.**




**WHEN THE TWISTLOCK IS ACCESSIBLE
FROM SIDE, USE TOOL: 5003-ET-2.**




**INSERT THE TOOL INTO THE SIDE-APERTURE
AND TWIST THE TOOL UNDERNEATH
THE UPPER CONE.**




**TWIST THE UPPER CONE COUNTER-CLOCKWISE
BY PULLING THE HANDLE.**



PUSH THE TUBE-SLEEVE INTO THE APERTURE.



**TWIST THE TOOL COUNTER-CLOCKWISE UNTIL THE
TOOL IS SECURED INSIDE THE CORNER CASTING.**



**MAKE SURE THAT THE TOOL IS SECURED
BEFORE LIFTING THE CONTAINER.**



EMERGENCY RELEASE TOOL


for CV-8 & CV-20 MANUAL TWISTLOCKS



MACGREGOR
ALLSET

MODEL 5003-OT-ER

for CV-8 & CV-20 Twistlocks



SUB FOR: MACGREGOR 1187900
MATERIAL: STRUCTURAL STEEL
FINISH: HOT-DIP GALVANIZED (HDG)
WEIGHT: 3.1 LBS / 1.4 Kg

BUFFERS USA INC 

"The Intermodal Hardware Specialists"

5003-5



904-696-0010

E-mail: sales@buffersusa.com

7/10/24